

AUTOQUIP AUTOMATION

Disposable 25cc Quick Flush Integrator Low Pressure

Custom Robotic Component



Use:

Replaces Graco Precision Mix™ or Robo Mix™ integrators to provide better mixing and flushing and faster color changes for low pressure applications. It's plastic inner tube can be replaced quickly and inexpensively.

Major Features:

- Immediate Payback - instantly reduces color change time and waste.
- Finless plastic material allows less adhesion of coatings, and therefore, results in even a quicker flush and less solvent usage.
- Throw the low-cost plastic inner tube away rather than clean it.
- Larger diameter of the inner tube cuts down the distance to the outer tube wall resulting in better cleaning and mixing.
- Same easy-to-install 3-piece design as metal high pressure version.
- Smaller diameter of outer assembly for better mixing and flushing.
- Tapered outlet for funneling of coatings and solvent.
- 2-piece outer tube constructed of stainless steel for durability and easy cleaning and flushing.




Autoquip, Inc.
N57 W13430 Reichert Avenue
Menomonee Falls, WI 53051
Phone: (262) 781-6133
Fax: (262) 781-6188

email: autoquip@mixcom.com

web site: www.aqautomation.com

**AUTOQUIP
AUTOMATION**



AUTOQUIP AUTOMATION

Quick Flush Integrator Parts

Pt. No.	Description	Pt. No.	Description
MY-535-P	<i>P-Mix/Pro Mix 50cc High Pressure Integrator</i>	JY-535-RUT	<i>Robo-Mix Inner Tube Top</i>
MY-535-POT	<i>P-Mix/Pro Mix 50cc Outer Tube</i>	LY-535-R	<i>Robo-Mix 25cc Disposable Integrator</i>
MY-535-PAP	<i>P-Mix Outer Tube Cap</i>	LY-535-ROT	<i>Robo-Mix 25cc Outer Tube</i>
MY-535-PIT	<i>P-Mix 50cc Inner Tube</i>	LY-535-RAP	<i>Robo-Mix Outer Tube Cap</i>
MY-535-POG	<i>#19 Teflon O-Ring</i>	LY-535-RDT	<i>Disposable 25cc Robo-Mix Integrator Tube</i>
MY-535-PTP	<i>Optional Threaded Cap for P-Mix</i>	LY-535-ROG	<i>#19 Teflon O-Ring</i>
KY-535-P	<i>P-Mix II 30cc Low Pressure Disposable Integrator</i>	LY-535-RTP	<i>Optional Threaded Cap for Robo-Mix</i>
KY-535-POT	<i>P-Mix II 30cc Outer Tube</i>	LY-535-RUG	<i>-21 7 Teflon O-Ring</i>
KY-535-PAP	<i>P-Mix Outer Tube Cap</i>	LY-535-RUT	<i>Robo-Mix Inner Tube Top</i>
KY-535-PDT	<i>Disposable 30cc P-Mix II Integrator Tube</i>	DY-535-P	<i>P-Mix II Modified Low Pressure Disposable Integrator</i>
KY-535-POG	<i>#19 Teflon O-Ring</i>	DY-535-POT	<i>P-Mix II Modified Outer Tube</i>
KY-535-PTP	<i>Optional Threaded Cap for P-Mix</i>	DY-535-PAP	<i>P-Mix Outer Tube Cap</i>
JY-535-P	<i>P-Mix II 25cc High Pressure Integrator</i>	DY-535-PDT	<i>Disposable 25cc P-Mix II Integrator Tube</i>
JY-535-POT	<i>P-Mix II 25cc Outer Tube</i>	DY-535-POG	<i>#19 Teflon O-Ring</i>
JY-535-PAP	<i>P-Mix II Outer Tube Cap</i>	DY-535-PTP	<i>Optional Threaded Cap for P-Mix</i>
JY-535-PIT	<i>P-Mix 25cc Inner Tube</i>	DY-535-P-TFE	<i>P-Mix II Modified Low Pressure Disposable Integrator, Teflon Coated</i>
JY-535-POG	<i>#19 Teflon O-Ring</i>	GY-535-P-TFE	<i>P-Mix II Modified Low Pressure Disposable Integrator, Teflon Coated</i>
JY-535-PTP	<i>Optional Threaded Cap for P-Mix</i>	-	<i>Disposbale Liner</i>
LY-535-P	<i>P-Mix II 25cc Low Pressure Disposable Integrator</i>	HY-535-P	<i>P-Mix II 50cc Low Pressure Disposable Integrator</i>
LY-535-POT	<i>P-Mix II 25cc Outer Tube</i>	HY-535-POT	<i>P-Mix II 50cc Outer Tube</i>
LY-535-PAP	<i>P-Mix Outer Tube Cap</i>	HY-535-PAP	<i>P-Mix Outer Tube Cap</i>
LY-535-PDT	<i>Disposable 25cc P-Mix II Integrator Tube</i>	HY-535-PDT	<i>Disposable 50cc P-Mix II Integrator Tube</i>
LY-535-POG	<i>#19 Teflon O-Ring</i>	HY-535-POG	<i>#19 Teflon O-Ring</i>
LY-535-PTP	<i>Optional Threaded Cap for P-Mix</i>	HY-535-PTP	<i>Optional Threaded Cap for P-Mix</i>
MY-535-R	<i>Robo Mix 50cc Integrator</i>	HY-535-R	<i>Robo-Mix 50cc Integrator, Disposable</i>
MY-535-ROT	<i>Robo-Mix 50cc Outer Tube</i>	HY-535-ROT	<i>Robo-Mix 50cc Outer Tube</i>
MY-535-RAP	<i>Robo-Mix Outer Tube Cap</i>	HY-535-RAP	<i>Robo-Mix Outer Tube Cap</i>
MY-535-RIT	<i>Robo-Mix 50cc Inner Tube</i>	HY-535-RIT	<i>Robo-Mix 50cc Inner Tube</i>
MY-535-ROG	<i>#19 Teflon O-Ring</i>	HY-535-ROG	<i>#19 Teflon O-Ring</i>
MY-535-RTP	<i>Optional Threaded Cap for Robo-Mix</i>	HY-535-RTP	<i>Optional Threaded Cap for Robo-Mix</i>
MY-535-RUG	<i>-2 17 Teflon O-Ring</i>	HY-535-RUG	<i>-21 7 Teflon O-Ring</i>
MY-535-RUT	<i>Robo-Mix Inner Tube Top</i>	HY-535-RUT	<i>Robo-Mix Inner Tube Top</i>
KY-535-R	<i>Robo-Mix 30cc Disposable Integrator</i>	3614-94-RBK	<i>RoboMix Manifold Repair Kit</i>
KY-535-ROT	<i>Robo-Mix 30cc Outer Tube</i>		
KY-535-RAP	<i>Robo-Mix Outer Tube Cap</i>		
KY-535-RDT	<i>Disposable 30cc Robo-Mix Integrator Tube</i>		
KY-535-ROG	<i>#19 Teflon O-Ring</i>		
KY-535-RTP	<i>Optional Threaded Cap for Robo-Mix</i>		
KY-535-RUG	<i>-21 7 Teflon O-Ring</i>		
KY-535-RUT	<i>Robo-Mix Inner Tube Top</i>		
JY-535-R	<i>Robo-Mix 25cc Integrator</i>		
JY-535-ROT	<i>Robo-Mix 25cc Outer Tube</i>		
JY-535-RAP	<i>Robo-Mix Outer Tube Cap</i>		
JY-535-RIT	<i>Robo-Mix 25cc Inner Tube</i>		
JY-535-ROG	<i>#19 Teflon O-Ring</i>		
JY-535-RTP	<i>Optional Threaded Cap for Robo-Mix</i>		
JY-535-RUG	<i>-21 7 Teflon O-Ring</i>		